


RadEye™ 4

Large Area Imager



Key Features:

- Large 2" by 4" active area
- Over two million pixels
- 10 lp/mm resolution
- Dynamic range >10,000:1
- Variable frame rate (0.01 – 4.5 Hz)
- Four parallel differential video outputs
- Fully integrated timing control
- Direct-coupled scintillator

The RadEye4 large-area image sensor continues the RadEye™ series' tradition of high performance and cost-effective value. The large 49.2 mm by 98.6 mm active area consists of a 1024 by 2048 matrix of silicon photodiodes on 48 μm centers. Several timing modes allow for high flexibility in signal integration and readout. The RadEye4 is available in a standard configuration to detect x-rays and other energetic radiation in the 10 kV to 50 kV range, as well as in the EV model for x-ray energy up to 160 kV. Its uses cover a wide range of imaging applications from medical diagnostics to industrial inspection (NDT) and scientific imaging.

Description:

The *RadEye4* large-area image sensor contains four individual *RadEye1* photodiode arrays along with their associated circuitry for scanning and readout. The four arrays operate in parallel and can be driven with a single set of control lines. They are aligned and mounted side-by-side on a common aluminum support base, resulting in a nearly seamless active area with a large 110 mm diagonal. The *RadEye4* module is packaged together with a scintillator in direct contact with the sensor, and a thin carbon-fiber window to protect the array. The EV model adds a fiber-optic faceplate (FOFP) between the scintillator and the sensor for added radiation resistance. Please note that the sensor enclosure is open towards the connector side and requires additional shielding against ambient light to operate the sensor.

The support and control functions for the *RadEye4* sensor are integrated on-chip to minimize the amount of external circuitry needed to run the imager. Five digital control inputs determine the integration and readout timing. In *continuous* mode (*START=high*) only an external pixel clock is required to run the device. In *frame* mode (*START=pulsed*) the frame rate and integration time can be controlled externally. Adjusting the *START* frequency controls the integration time or synchronizes the imager to an external trigger such as the firing of an x-ray source (see timing diagrams on next page). To assure proper initialization of the on-chip control circuitry, the sensor should always be powered up in frame mode.

Each frame consists of 1024 lines of pixel data. A line consists of 2048 pixels (512 pixels on each output) plus a blanking period. A *rising edge* on the *START* input triggers the beginning of each frame readout. *START* must return to a *low* level before the readout cycle ends. If *START* remains *high*, the next readout cycle begins immediately following the last line of the previous frame. The maximum *CLOCK* frequency is 2.5 MHz, which corresponds to a maximum frame rate of 4.5 frames per second (fps). In *continuous* mode, it is also possible to control the frame rate by adjusting the *CLOCK* frequency.

The *RadEye4* imager provides differential high-speed video signals from four parallel video outputs. The dark level on each output lies approximately 1.8 V below the reference voltage *VD*. The positive video outputs (*OUTS*) are pulsed above the dark level for each pixel, whereas the negative video outputs (*OUTR*) are pulsed below. At saturation, the two outputs will swing approximately 0.7 V above and below the dark level. The conversion gain for the differential signal (*OUTS* – *OUTR*) is 0.5 μV per electron.

Specifications:

Avg. dark current (at 23°C) ...4000 electrons/sec*
Read noise (rms, at 1 fps).....150 electrons
Saturation.....2,800,000 electrons
Dynamic range85 dB (>14 bits)
Frame rate.....0.01 to 4.5 fps
Max. data rate (each output)2.5 MHz
Conversion gain0.5 μV /electron
Supply voltage (*VDD*).....5 V (± 0.25 V)
Supply current4 x 25 mA (typ)
Reference voltage (*VD*)3.8 V (± 0.5 V)
Analog output +2 V (dark) to 2.7 V (sat)
Analog output –2 V (dark) to 1.3 V (sat)
Digital “low” voltage.....0.5 V max.
Digital “high” voltage4.0 V min.
Operating temperature0 to 50 °C
Storage temperature-25 to +85 °C

* dark current doubles approx. every 8°C


Connector Pinout:

Pin	Type	Signal	Description
1		VDD	Power (+5V)
2		GND	Ground
3	A	OUTS	Video Output +
4	A	OUTR	Video Output -
5		GND	Ground
6	A	VD	Reference In
7		GND	Ground
8	D	RESET	Array Reset In
9	D	START	Frame Start In
10	D	CLOCK	Master Clock In
11	D	BIN	Binning Select In
12	D	NDR	NDR Select In
13	D	FRAME	Frame Sync Out
14	D	LINE	Line Sync Out
15		GND	Ground


Type: A = Analog Signal D = Digital Signal

Timing Diagrams:

1. Continuous Mode (START is always high)




2. Frame Mode (START is pulsed)



Additional Timing Modes:


The BIN and RESET inputs offer additional control over the readout functions. The BIN input, when *high*, causes the readout to skip every other row and column. This shortens the readout time and raises the maximum frame rate to 17.4 fps. A *high* level on the RESET input causes an asynchronous reset of all photodiodes in the active area. This feature can be used to reset the dark signal prior to an exposure.

The *RadEye4* also features a non-destructive readout (NDR) mode that is activated by setting the NDR input to a *high* level. In this mode, the voltage at each pixel is sampled without resetting the photodiode. This feature can be used to monitor the exposure level in the device, or to implement a low-noise readout mode by reading out and subtracting two images before and after an exposure. Both analog outputs carry the same signal when NDR is turned on. There is a slight increase in fixed-pattern noise when the NDR mode is activated, which can be compensated for by performing the appropriate offset correction in software. Please refer to *Rad-ikon Application Note AN04* for more information on the RadEye sensor timing and using the NDR mode.



Detector resolution with various scintillators.

Mechanical Dimensions:



Samtec FC1 Series
P/N FC1-15-02-T-WT
(mates with FJ Series
flex cable jumper)

The *RadEye4* module contains four individual *RadEye1* sensors that are mounted side-by-side and aligned to each other with sub-pixel accuracy. Three small gaps, each approximately two pixels wide, separate the four sections of the active area. Four identical 15-pin flex cable connectors (Samtec P/N FC1-15-02-T-WT) provide power and signal connections to the sensors. Except for the output signals from each sensor (pins 3, 4, 13 and 14) all pins can be connected in parallel.

Depending on the application, it may be possible to ignore the gaps between the four image sections and simply merge the images together. Another option is to interpolate the missing information across the gaps. Please refer to *Rad-icon Application Note AN03* for more detailed information regarding this topic.

Ordering Information:

Rad-icon P/N	Description
RE1029	RadEye4 (low dose, 10-50 kV)
RE1061	RadEye4 EV (high dose, 10-160 kV)
-01	Premium Grade ¹ , Min-R 2190 Scintillator
-02	Standard Grade ² , Min-R 2190 Scintillator
-03	Premium Grade, Lanex Fine Scintillator
-04	Standard Grade, Lanex Fine Scintillator

¹ no line defects ² up to seven line defects

The standard *RadEye4* module is packaged with a Gd₂O₂S scintillator (Kodak Min-R 2190 or Lanex Fine) and a 1 mm thick graphite window. Other scintillator and window options may be available on request.